





Capillary Ultrafiltration Module

HYDRAcap[®]80

Performance[†] Filtrate Flow: 16.3 – 39.5 gpm (3.7 – 9.0 m³/h)

Filtrate Turbidity: \leq 0.07 NTU Virus removal: \geq 4 log Bacteria removal: \geq 4 log

Type Configuration: Capillary Ultrafiltration Module

Membrane Polymer: Hydrophilic Polyethersulfone Nominal Membrane Area: 670 ft² (62.2 m²)

Fiber Dimensions: ID 0.031" (0.8 mm), OD 0.055" (1.4 mm)

Pore size: 0.02 micron

Application Data[‡] Typical Filtrate Flux Range: 35 – 85 gfd (59 – 145 l/m²/h)

Maximum Applied Feed Pressure: 73 psig (5 bar)

Maximum Transmembrane Pressure: 20 psig (1.4 bar)

Maximum Backwash Transmembrane Pressure: 20 psig (1.4 bar)

Instantaneous Chlorine Tolerance: 100 ppm...

Instantaneous Hydrogen Peroxide Tolerance: 200 ppm...

Instantaneous Hydrogen Peroxide Tolerance: 200 ppm

Maximum Chlorine Exposure: 100,000 ppm-hrs

Maximum Instantaneous Feed Turbidity: 100 NTU

Maximum Operating Temperature: 104 °F (40 °C)

pH Operating Range: 4.0 - 10.0

Cleaning pH Range: 1.5 – 13.0

Operating Mode: Inside to Outside Filtration

Direct flow or Crossflow


Typical Process Conditions

Backwash Flux: 100 – 150 gfd (170 – 255 l/m²/h)

Backwash Duration: 30 – 60 seconds
Backwash Frequency: 20 – 60 minutes
Chemical Enhanced Backwash Frequency: 0 – 4 times per day

Chemical Enhanced Backwash Frequency: 0 – 4 times per day Chemical Enhanced Backwash Duration: 1 – 30 minutes

 $\begin{array}{ll} \mbox{Disinfection Chemicals:} & \mbox{NaOCI, H_2O_2, CIO_2 or NH_2CI} \\ \mbox{Cleaning Chemicals:} & \mbox{NaOH, HCI, H_2SO_4, or $Citric Acid} \\ \end{array}$



A, inches (mm)	B, inches (mm)	C, inches (mm)	Pipe connections	Weight, lbs. (kg) ave.
83 (2108)	86 1/8 (2188)	87 1/4 (2216)	2" Victaulic	120 (54)

Certifications:

NSF61, CDPH, and ETV-NSF Verification

At 68°F (20°C).

** For 15 minutes or less.

[†] Typical module performance for most feedwaters.

Notice: Weight stated is shipping weight including 1L of a 0.95% solution of sodium bisulfite preservative. Hydranautics also offers HYDRAcap®80-NON, which is a dummy module with no potting or fiber.

Hydranautics believes the information and data contained herein to be accurate and useful. The information and data are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. Hydranautics assumes no liability for results obtained or damages incurred through the application of the presented information and data. It is the user's responsibility to determine the appropriateness of Hydranautics' products for the user's specific end uses. 1/15/14



[‡] The limitations shown here are for general use. The values may be more conservative for specific projects to ensure the best performance and longest life of the membrane.